

Project: _____

Item #: _____ Quantity: _____

Model #: _____



Order Guide:

Model SM-651C-T

MAX INDUCTION™

Countertop, Portable, *Hold-Only* Induction Warmer With Titanium Colored, Stainless Base

- SM-651C-T (110 Volt / US)
- SM-653C-T (220-240 Volt / Int'l)
- SM-653CU-T (220-240 Volt / Int'l)

✓	Model Number	Voltage	Peak Power	Plug Type
	SM-651C-T (US)	110-120	650 Watts	NEMA 5-15

Simple, Solid State Controls With:

- Power ON/OFF Touch Pad
- Power ON/Pan-Present Indicator Lights
- Four Set-Hold, Touch Pad Temperature Controls

Short Form Specification:

Specified unit to be a Spring USA **MAX Induction™** SM- 651C-T, Countertop, Portable, **Hold-Only** Induction Warmer, with low-profile design, titanium-colored stainless steel case, 5mm thick tempered glass cook top and integrated oversized pan support. Unit features our exclusive Spring USA SmartScan® technology with over/under voltage protection, pan size and pan type recognition, large touch-screen power/temp display; plus all the following features.

Construction & Performance Features:

- Tempered, sleek, black smoked glass faceplate
- Attractive, durable, easy to clean, titanium-colored stainless steel body design
- Reinforced, tempered glass vessel surface
- Features non-skid, non-scratch footing
- 100% Silicon rubber protective top seal
- Energy Saving, 650 watts of power; perfect for product holding
- Four, Touch-Control Temperature Settings
- Low-Profile Design, Only 3-1/8" Tall
- Exclusive SmartScan® Process Controller adjusts for voltage, pan size and pan type

Low	Low-Med	Med-High	High
145 - 155° F	156 - 165° F	166 - 175° F	176 - 185° F
61 - 71° C	72 - 76° C	77 - 82° C	83 - 87° C

- Light-Up Temperature Indicator
- SmartScan® Over/Under Voltage Protection
- Pan Overheat Protection
- Tempered, Black Glass Control Panel Overlay
- Durable, Stick-Resistant, Whitford, 2-Ply, Quantanium Coating

Standard Warranty:

- One Year, Parts & Labor

Agency Listings:

- FCC
- ETL
- ETL-Sanitation to NSF-4
- CETL

Available Accessories/Alternate Configurations:

- Storage & Transport Box [Spring USA Catalog]
- Induction-Ready Cookware [Spring USA Catalog]
- Induction-Ready Serving Vessels [Spring USA Catalog]
- AF350 Under-Counter Air Filter System [See Spec.SIR-7]
- Built-In, High-Power Induction Ranges [See Spec.SIR-3]
- Custom Tabletop Induction Featuring SmartStone™
- Countertop (Hold-Only) Induction Hot Plate [Spec.SIR-2]
- Mobile & Custom Configurations [Contact Spring USA]

MAX INDUCTION™

Countertop, Portable, *Hold-Only* Induction Warmer With Titanium Colored, Stainless Base

● SM-651C-T (110 Volt / US)



[EC] Electric Requirements:

Model	Voltage	Phase	Hertz	Watts	Amps	Plug
SM-651C-T	110-120	1	50-60	650	5.4	NEMA 5-15P (6' Cord)

Key Dimensions & Shipping Information:

Model	Unit Width	Unit Length	Unit Height	Shipping Weight *	Single Unit Shipping Carton *		
					Width	Length	Height
SM-651C-T	12.5"	16"	3-1/8"	13 lbs.	15-1/2"	18"	4-1/2"

* SM-651C-T Two Unit Case Pack: Weight = 29 lbs. (13.1 kg); Length = 22" (559 mm); Width = 19" (483 mm); Height = 16" (406 mm)

Notes & Conditions:

1. Ensure that you have dedicated power wherever you are planning to use your induction warmer. Each warmer draws 5.4 Amps. Up to three units can operate from one single, 20 Amp, dedicated circuit (US Models).
2. For optimum performance, allow 4" (102 mm) rear and side clearance for good air circulation. **Your induction warmer must have proper ventilation at all times.** Do not place your induction unit next to any appliance that throws heat; such as a stove, oven or fryer. Actual range temperature may vary due to a number of variables, such as ambient temperature in the immediate surrounding area, content and volume of food being heated or cooked, and whether or not you are using a lid on the serving vessel. Refer to your Operations Manual for steps on how to properly clean and maintain your induction warmer.
3. This induction warmer requires the use of ferrous metal, induction-ready cookware.